

YCS34, Copper Loop Splice

By Burndy
Catalog # [YCS34](#)



CU loop splice connector designed to withstand jumper loop tensile and vibration stresses up to 60 percentage RBS, Index: 210

Features

- Copper Loop Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	500 kcmil
Range	
Conductor - Copper Str Size	500 kcmil

Configuration

Physical Attribute - Number of	2
Crimps Required	
Connector Type	Splice

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	2-1/2 in
Package Weight	0.000 lb.
Package Length	0.000 in

Package Width	0.000 in
Dimension - L Length Overall	130 mm
mm	
Dimension - B Length inch	2.5 in
Dimension - B Outside	1.38 in
Diameter inch	
Dimension - A Outside	1.38 in
Diameter inch	
Dimension - Length Overall	5.12 in
inch	

General

Plated	N
Trade Name	HYSPLICE™
Die Index	210
UPC	781810820605
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810820605

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1480
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)