

YCS361R, Aluminum Sleeve, Staked Cable Stop

By Burndy
Catalog # [YCS361R](#)

HYSPLICE AL sleeve with staked cable stop, designed to withstand jumper loop tensile and vibration stresses. ANSI C119.4 CLASS 2 (PARTIAL TENSION), Index: 327.

Features

- HYSPLICE Sleeve designed to withstand jumper loop tensile and vibration stresses
- Made of aluminum with staked-in cable stop
- Pre-Filled with PENETROX Joint Compound and Capped

Application

For ACSR, All Aluminum, 6201, 5005 And Compressed Conductors

Specifications


Buy American Compliant Certification - cULus	Contact Manufacturer No
EU RoHS Indicator	Contact Manufacturer
Certification - UL Recognized	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Str Size	477.0 (18/1) Pelican kcmil
Conductor - ACSR Str Size Range	477.0 (18/1) Pelican kcmil
Conductor - AL Str Size	477 kcmil (18/1)
Conductor - AL Str Size Range	477 kcmil

Configuration

Connector Type	Splice
----------------	--------



Dimensions

Dimension - Outside Diameter inch	1.3 in
Dimension - L Length Overall mm	210 mm
Dimension - B Length fraction	4-3/50 in
Dimension - B Length inch	4.06 in
Dimension - Length Overall inch	8.25 in

General

Die Index	327
Trade Name	HYSPLICE™
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Plated	N
Type	YCS-R
UPC 12 Digit	781810820575
UPC 14 Digit GTIN	00781810820575
Material	Aluminum
Plating Type	Unplated
UPC	781810820575

Logistics

Minimum Pack Quantity	25
Carton Quantity	25
Pallet Quantity	3600

Product Assets

[Catalog \[English\]](#)