

YCS39, Copper Loop Splice

By Burndy
Catalog # [YCS39](#)



CU loop splice connector designed to withstand jumper loop tensile and vibration stresses up to 60 percentage RBS, Index: 627

Features

- Copper Loop Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	750 kcmil
Conductor - Copper Str Size	750 kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - B Length fraction	3 in
Dimension - L Length Overall mm	175 mm
Dimension - B Length inch	3.01 in
Dimension - B Outside Diameter inch	1.7 in

Dimension - A Outside Diameter inch	1.7 in
Dimension - Inside Diameter inch	1.06 in
Dimension - Length BB inch	3.01 in
Dimension - Length Overall inch	6.88 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	627
UPC	781810014271
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810014271
UPC 14 Digit GTIN	00781810014271

Logistics

Minimum Pack Quantity	1
Pallet Quantity	480
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)