



YCS391A, Aluminum Sleeve

By Burndy
Catalog # [YCS391A](#)



Aluminum sleeve designed to withstand jumper loop tensile and vibration stresses. Made of aluminum with staked cable stop. ANSI C119.4 CLASS 1A(PARTIAL TENSION),Die Index: 342.

Features

- HYSPLICE Sleeve designed to withstand jumper loop tensile and vibration stresses
- Made of aluminum with staked-in cable stop
- Pre-Filled with PENETROX Joint Compound and Capped

Application

For All Aluminum, Compressed And Compact Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	750 (37) kcmil
Conductor - ACAR Str Size	750 (37) kcmil
Conductor - AL Str Size	759 kcmil (1.026)
Conductor - AL Str Size Range	8 AWG
Conductor - ACSS Str Size Range	795 (54/7) kcmil
Conductor - ACSS Str Size	795 (54/7) kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	265 mm
mm	
Dimension - Outside Diameter	1.67 in
inch	
Dimension - B Length fraction	5-4/25 in
Dimension - B Length inch	5.16 in
Dimension - Length Overall	10.44 in
inch	

General

Trade Name	HYSPLICE™
Die Index	342
Prefilled Oxide Inhibitor	Y
Plated	N
Sub Brand	HYSPLICE
UPC	781810015155
Type	YCS-A
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810015155
UPC 14 Digit GTIN	00781810015155

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1344
Carton Quantity	8

Product Assets

[Catalog \[English\]](#)