

YCS39R, Aluminum Sleeve, Staked Cable Stop

By Burndy
Catalog # [YCS39R](#)

HYSPLICE AL sleeve with staked cable stop, designed to withstand jumper loop tensile and vibration stresses. ANSI C119.4 CLASS 2 (PARTIAL TENSION), 10-3/4 IN L

Features

- Aluminum Sleeve
- Staked Cable Stop

Specifications


Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - AAAC 5005 Size Range	652.4 (19) kcmil
Conductor - AAAC 6201 Size Range	652.4 (19)
Conductor - AAAC 6201 Size Range	652.4 (19)
Conductor - ACSR Str Size	• 556.5 (24/7) Parakeet • 556.5 (26/7) Dove
Conductor - ACSR Str Size Range	556.5 (24/7) Parakeet-556.5 (26/7) Dove
Conductor - AL Str Size	556.5
Conductor - AL Str Size Range	556.5
Conductor - AAAC 5005 Size	652.4 (19)

Configuration

Connector Type	Splice
----------------	--------



Dimensions

Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length fraction	5-22/71 in
Package Weight	0.000 lb.
Dimension - B Length inch	5.31 in
Dimension - L Length Overall mm	273 mm
Package Height	0.000 in
Dimension - Length Overall inch	10.75 in

General

Die Index	608
Trade Name	HYSPLICE™
Plated	N
Prefilled Oxide Inhibitor	Y
UPC 12 Digit	781810015070
UPC 14 Digit GTIN	00781810015070
Material	Aluminum
Plating Type	Unplated
UPC	781810015070

Logistics

Minimum Pack Quantity	10
Carton Quantity	10
Pallet Quantity	1680

Product Assets

[Catalog \[English\]](#)