



YCS43R, Aluminum Sleeve, Staked Cable Stop

By Burndy
Catalog # [YCS43R](#)

HYSPLICE AL sleeve with staked cable stop, designed to withstand jumper loop tensile and vibration stresses. ANSI C119.4 CLASS 2 (PARTIAL TENSION), 10-5/8 IN L.

Features

- HYSPLICE Sleeve designed to withstand jumper loop tensile and vibration stresses
- Made of aluminum with staked-in cable stop
- Pre-Filled with PENETROX Joint Compound and Capped

Application


For ACSR, All Aluminum, 6201, 5005 And Compressed Conductors

Specifications

Buy American Compliant Certification - cULus	Contact Manufacturer
EU RoHS Indicator	No
Certification - UL Recognized	Yes
Buy America(n) Qualified	No
Certification - ETL	Contact Manufacturer
Standards - RoHS Compliance Status	No
Certification - CSA Approved	CM
UL Listed	No

Conductor

Conductor - AAAC 5005 Size Range	740.8 (37) kcmil
Conductor - AAAC 6201 Size	740.8 (37) kcmil
Conductor - AAAC 6201 Size Range	740.8 (37) kcmil
Conductor - ACSR Str Size	• 605 (30/19) Teal kcmil • 636 (24/7) Rook kcmil • 636 (26/7) Grosbeak kcmil • 636 (30/19) Egret kcmil • 666.6 (24/7) Flamingo kcmil
Conductor - ACSR Str Size Range	605 (30/19) Teal kcmil-666.6 (24/7) Flamingo kcmil
Conductor - AL Str Size	636 kcmil
Conductor - AL Str Size Range	636 kcmil
Conductor - AAAC 5005 Size	740.8 (37) kcmil



Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	270 mm
Package Height	0.000 in
Dimension - B Length fraction	5-1/4 in
Dimension - B Length inch	5.25 in
Dimension - Length Overall inch	10.62 in

General

Die Index	• 292 • 319
Trade Name	HYSPLICE™
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Plated	N
Type	YCS-R
UPC 12 Digit	781810015087
UPC 14 Digit GTIN	00781810015087
Material	Aluminum
Plating Type	Unplated
UPC	781810015087

Logistics

Minimum Pack Quantity	10
Carton Quantity	10
Pallet Quantity	900

Product Assets

[Catalog \[English\]](#)