

YCS44, Copper Loop Splice

By Burndy
Catalog # [YCS44](#)



CU loop splice connector designed to withstand jumper loop tensile and vibration stresses up to 60 percentage RBS, 7-3/4 IN L

Features

- Copper Loop Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	1000 kcmil
Conductor - Copper Str Size	1000 kcmil

Configuration

Physical Attribute - Number of Crimps Required	4
Connector Type	Splice

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	3-9/53 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Dimension - L Length Overall mm	195 mm
Dimension - B Length inch	3.17 in
Dimension - B Outside Diameter inch	2 in
Dimension - A Outside Diameter inch	2 in
Dimension - Length BB inch	3.17 in
Dimension - Length Overall inch	7.69 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	345
UPC	781810014141
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810014141
UPC 14 Digit GTIN	00781810014141

Logistics

Minimum Pack Quantity	1
Pallet Quantity	300
Carton Quantity	5

Product Assets

[Catalog \[English\]](#)