

YCS49R, Aluminum Splice, Single Sleeve Jumper

By Burndy
Catalog # [YCS49R](#)

Al Tube Compression Splice, Single Sleeve Jumper Partial
Tension, 954 - 1033.5 kcmil ACSR

Features

- Aluminum Splice
- Single Sleeve Jumper

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor


Conductor - ACSR Str Size	• 954 (54/7) Cardinal kcmil • 1033.5 (45/7) Ortolan kcmil • 1033.5 (54/7) Curlew kcmil
Conductor - ACSR Str Size Range	954 (54/7) Cardinal kcmil-1033.5 (54/7) Curlew kcmil
Conductor - AL Str Size	954 kcmil
Conductor - AL Str Size Range	954 kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Length	0.000 in
----------------	----------



Package Width	0.000 in
Dimension - B Length fraction	6-1/10 in
Package Weight	0.000 lb.
Dimension - B Length inch	6.1 in
Dimension - L Length Overall mm	313 mm
Package Height	0.000 in
Dimension - Length Overall inch	12.32 in

General

Die Index	575
Trade Name	HYSPLICE™
Plated	N
Prefilled Oxide Inhibitor	Y
UPC 12 Digit	781810129425
UPC 14 Digit GTIN	00781810129425
Material	Aluminum
Plating Type	Unplated
UPC	781810129425

Logistics

Minimum Pack Quantity	8
Carton Quantity	8
Pallet Quantity	720

Product Assets

[Catalog \[English\]](#)