

YCS4R, Aluminum Sleeve, Staked Cable Stop

By Burndy
Catalog # [YCS4R](#)

HYSPLICE AL sleeve with staked cable stop, designed to withstand jumper loop tensile and vibration stresses. ANSI C119.4 CLASS 2 (PARTIAL TENSION),Index:237

Features

- Aluminum Sleeve
- Staked Cable Stop


Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - AAAC 5005 Size Range	48.69 (7) kcmil
Conductor - AAAC 6201 Size Range	48.69 (7) kcmil
Conductor - ACSR Cmpt Size Range	4 AWG
Conductor - ACSR Str Size Range	4 (6/1) Swan AWG-4 (7/1) Swanate AWG
Conductor - AL Str Size Range	4 AWG (7)
Conductor - AAAC 5005 Size	48.69 (7) kcmil

Configuration



Connector Type Splice

Dimensions

Dimension - B Length fraction	2-19/50 in
Dimension - B Length inch	2.38 in
Dimension - Outside Diameter inch	0.4 in
Dimension - L Length Overall mm	125 mm
Dimension - Length Overall inch	4.91 in

General

Die Index	237
Trade Name	HYSPLICE™
Plated	N
Prefilled Oxide Inhibitor	Y
UPC 12 Digit	781810014981
UPC 14 Digit GTIN	00781810014981
Material	Aluminum
Plating Type	Unplated
UPC	781810014981

Logistics

Minimum Pack Quantity	1
Carton Quantity	25
Pallet Quantity	24000

Product Assets

[Catalog \[English\]](#)