



YCT2626, 1-piece Tap Connector

By Burndy
Catalog # [YCT2626](#)



One-piece, copper compression tap connector with U-shaped run element and tubular tap for joining hard and medium-hard drawn copper,Die index:166

Features

- Copper Compression Tap Connector
- 1-piece

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	2/0 AWG
Conductor - Copper Str Run	2/0 AWG
Conductor - Copper Str Tap Range	2/0 AWG
Conductor - Copper Str Tap	2/0 AWG

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - Height mm	82.8 mm
Dimension - Height inch	3.26 in
Dimension - Height fraction	3-1/4
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Dimension - L Length Overall mm	143 mm
Dimension - Outside Diameter inch	0.71 in
Dimension - Width fraction	1-7/50 in
Dimension - B Length fraction	1-1/11 in
Dimension - Width mm	25 mm
Dimension - Width inch	0.97 in
Dimension - B Length inch	1.09 in
Dimension - Length BB inch	1.7 in
Dimension - Length Overall inch	5.62 in

General

Trade Name	HYTEE™
Die Index	166
Die Index Run Side	166
Die Index Tap Side	166
Prefilled Oxide Inhibitor	N
Plated	Y
UPC	781810014332
Material	Copper
Plating Type	Tin
UPC 14 Digit GTIN	00781810014332

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3712
Carton Quantity	8

Product Assets

[Catalog \[English\]](#)