



YCT2828, 1-piece Tap Connector

By Burndy
Catalog # [YCT2828](#)



One-piece, copper compression tap connector with U-shaped run element and tubular tap for joining hard and medium-hard drawn copper,Die index:168

Features

- Copper Compression Tap Connector
- 1-piece

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	4/0 AWG
Conductor - Copper Str Run	4/0 AWG
Conductor - Copper Str Tap Range	4/0 AWG
Conductor - Copper Str Tap	4/0 AWG

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - Height mm	101.6 mm
Dimension - Height inch	4.00 in
Dimension - Height fraction	4
Dimension - B Length fraction	81/89 in
Package Weight	0.000 lb.

Dimension - Width mm	30 mm
Dimension - Width inch	1.2 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	145 mm
Dimension - B Length inch	0.91 in
Dimension - Outside Diameter inch	0.89 in
Dimension - Width fraction	1-1/5 in
Dimension - Length BB inch	1.62 in
Dimension - Length Overall inch	5.72 in

General

Plated	Y
Die Index	168
Die Index Run Side	168
UPC	781810014349
Die Index Tap Side	168
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Tin
UPC 14 Digit GTIN	00781810014349

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1800
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)