

YCT2C2C, 1-piece Tap Connector

By Burndy
Catalog # [YCT2C2C](#)



One-piece, copper compression tap connector with U-shaped run element and tubular tap for joining hard and medium-hard drawn copper.

Features

- Copper Compression Tap Connector
- 1-piece

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	2 AWG
Conductor - Copper Str Run	2 AWG
Conductor - Copper Str Tap Range	2 AWG
Conductor - Copper Str Tap	2 AWG

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - Height mm	64.3 mm
Dimension - Height inch	2.53 in
Dimension - Height fraction	2-9/17 in
Dimension - B Length fraction	24/25 in

Dimension - Width mm	17 mm
Dimension - Width inch	0.68 in
Dimension - L Length Overall mm	123 mm
Dimension - B Length inch	0.96 in
Dimension - Outside Diameter inch	0.5 in
Dimension - Width fraction	17/25 in
Dimension - Length BB inch	1.03 in
Dimension - Length Overall inch	4.84 in

General

Plated	Y
Trade Name	HYTEE™
Die Index Run Side	163
UPC	781810184714
Die Index Tap Side	163
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Tin - Electro Plated
UPC 14 Digit GTIN	00781810184714

Logistics

Minimum Pack Quantity	1
Pallet Quantity	7200
Carton Quantity	40

Product Assets

[Catalog \[English\]](#)