



YCU25, Copper Repair Sleeve

By Burndy
Catalog # [YCU25](#)

Sheet Cu Repair Sleeve For Compression Splices(Single Sleeve
Jumper Normal Tension), 1/0 AWG Cu, 165 Index

Features

- Copper Repair Sleeve

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	1/0 AWG
Conductor - Copper Str Size	1/0 AWG

Configuration

Physical Attribute - Number of Crimps Required	4
Connector Type	Splice

Dimensions

Dimension - Height mm	19 mm
-----------------------	-------

Dimension - Height inch	0.74 in
Dimension - Height fraction	37/50 in
Dimension - Width inch	0.65 in
Dimension - L Length Overall mm	139 mm
Dimension - Width fraction	13/20 in
Dimension - Length Overall inch	5.47 in

General

Plated	N
Die Index	165
UPC	781810014370
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014370

Logistics

Minimum Pack Quantity	1
Pallet Quantity	5800
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)