



YCU26, Copper Repair Sleeve

By Burndy
Catalog # YCU26

Sheet Cu Repair Sleeve For Compression Splices(Single Sleeve
Jumper Normal Tension), 2/0 AWG Cu, 166 Index

Features

- Copper Repair Sleeve

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	2/0 AWG
Conductor - Copper Str Size	2/0 AWG

Configuration

Physical Attribute - Number of Crimps Required	4
Connector Type	Splice

Dimensions

Dimension - Height mm	21 mm
-----------------------	-------

Dimension - Height inch	0.83 in
Dimension - Height fraction	39/47 in
Dimension - Width inch	0.74 in
Dimension - L Length Overall mm	150 mm
Dimension - Width fraction	37/50 in
Dimension - Length Overall inch	5.91 in

General

Plated	N
Die Index	166
UPC	781810014387
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014387

Logistics

Minimum Pack Quantity	1
Pallet Quantity	4350
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)