



YCU27, Copper Repair Sleeve

By Burndy
Catalog # [YCU27](#)

Sheet Cu Repair Sleeve For Compression Splices(Single Sleeve
Jumper Normal Tension), 3/0 AWG Cu, 167 Index

Features

- Copper Repair Sleeve

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	3/0 AWG
Conductor - Copper Str Size	3/0 AWG

Configuration

Physical Attribute - Number of Crimps Required	5
Connector Type	Splice

Dimensions

Dimension - Height mm	24 mm
-----------------------	-------

Dimension - Height inch	0.93 in
Dimension - Height fraction	40/43 in
Dimension - Width inch	0.83 in
Dimension - L Length Overall mm	174 mm
Dimension - Width fraction	39/47 in
Dimension - Length Overall inch	6.84 in

General

Plated	N
Die Index	167
UPC	781810014394
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014394

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2940
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)