



YCU28, Copper Repair Sleeve

By Burndy
Catalog # [YCU28](#)

Sheet Cu Repair Sleeve For Compression Splices(Single Sleeve
Jumper Normal Tension), 4/0 AWG Cu, 168 Index

Features

- Copper Repair Sleeve

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - CopperWeld Str Size	3/0 V AWG
Conductor - Copper Str Size Range	4/0 AWG
Conductor - Copper Str Size	4/0 AWG

Configuration

Physical Attribute - Number of Crimps Required	6
Connector Type	Splice

Dimensions

Package Height	0.000 in
Dimension - Height mm	26 mm

Dimension - Height inch	1.04 in
Dimension - Height fraction	1-1/25 in
Package Weight	0.000 lb.
Dimension - Width inch	0.92 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	176 mm
Dimension - Width fraction	23/25 in
Dimension - Length Overall inch	6.91 in

General

Plated	N
Die Index	168
UPC	781810014400
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014400

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1960
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)