



YCU2C, Copper Repair Sleeve

By Burndy
Catalog # [YCU2C](#)

Sheet Cu Repair Sleeve For Compression Splices(Single Sleeve
Jumper Normal Tension), #2 AWG (7 Str) Cu, 163 Index

Features

- Copper Repair Sleeve

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	2 AWG
Conductor - Copper Str Size	2 AWG

Configuration

Physical Attribute - Number of Crimps Required	12
Connector Type	Splice

Dimensions

Dimension - Height mm	15 mm
-----------------------	-------

Dimension - Height inch	0.6 in
Dimension - Height fraction	3/5 in
Dimension - Width inch	0.54 in
Dimension - L Length Overall mm	89 mm
Dimension - Width fraction	27/50 in
Dimension - Length Overall inch	3.5 in

General

Plated	N
Die Index	163
UPC	781810014356
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014356

Logistics

Minimum Pack Quantity	800
Pallet Quantity	14500
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)