



YCU4C, Copper Repair Sleeve

By Burndy
Catalog # [YCU4C](#)

Sheet Cu Repair Sleeve For Compression Splices(Single Sleeve
Jumper Normal Tension), #4 AWG (7 Str) Cu, 162 Index

Features

- Copper Repair Sleeve

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	4 AWG
Range	
Conductor - Copper Str Size	4 AWG

Configuration

Physical Attribute - Number of	12
Crimps Required	
Connector Type	Splice

Dimensions

Dimension - Height mm	12 mm
-----------------------	-------

Dimension - Height inch	0.48 in
Dimension - Height fraction	12/25 in
Dimension - Width inch	0.43 in
Dimension - L Length Overall mm	83 mm
Dimension - Width fraction	3/7 in
Dimension - Length Overall inch	3.28 in

General

Plated	N
Die Index	162
UPC	781810014363
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014363

Logistics

Minimum Pack Quantity	1
Pallet Quantity	28800
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)