



YDR25G2, Copper Splice

By Burndy
Catalog # [YDR25G2](#)

Cu Compression splice, 1/0 str(Brl A) 1/0 sol(Brl B), 6.81"L

Features

- Compression Copper Splice

Application

Sleeves are tapered or chamfered at the ends, externally to provide gradual reduction of pressure on the conductor, and internally to facilitate conductor insertion

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	1/0
Conductor - Copper Str Size A Range	1/0
Conductor - Copper Solid Size B	2/0 AWG

Configuration

Physical Attribute - Number of Crimps Required	2
Physical Attribute - Number of Holes	6
Connector Type	Reducer

Dimensions

Dimension - B Length fraction	3-2/67 in
Dimension - L Length Overall	173 mm
Dimension - B Length inch	3.03 in
Dimension - B Outside Diameter inch	0.61 in
Dimension - A Outside Diameter inch	0.66 in
Dimension - Length BB inch	3.03 in
Dimension - Length Overall inch	6.81 in

General

Plated	N
Trade Name	HYREDUCER™
Sub Brand	REDUCER SPLICES
Die Index	• 165 • 287
UPC	781810014431
Type	YDR
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014431

Logistics

Minimum Pack Quantity	1
Pallet Quantity	4900
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)