



YDR2CG2, Copper Splice

By Burndy
Catalog # [YDR2CG2](#)

Cu Compression splice, #2 (Str) & #2 (Sol), 4.48"L

Features

- Copper Compression Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	2 AWG
Conductor - Copper Str Size A Range	2 AWG
Conductor - Copper Solid Size B	2 AWG

Configuration

Physical Attribute - Number of Crimps Required	6
Connector Type	HyReducer

Dimensions

Dimension - B Length fraction	1-10/11 in
-------------------------------	------------

Dimension - L Length Overall mm	114 mm
Dimension - B Length inch	1.91 in
Dimension - B Outside Diameter inch	0.48 in
Dimension - A Outside Diameter inch	0.52 in
Dimension - Length BB inch	1.91 in
Dimension - Length Overall inch	4.48 in

General

Plated	N
Trade Name	HYREDUCER™
Die Index	163
UPC	781810014417
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014417

Logistics

Minimum Pack Quantity	50
Pallet Quantity	11600
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)