



YDR4WG1, Copper Reducer

By Burndy
Catalog # [YDR4WG1](#)

Copper Hyreducer, # 4 Sol. (Barrel A) , #6 Sol. (Barrel B)

Features

- Compression Copper Reducer

Application

Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size A	4 AWG
Conductor - Copper Solid Size B	6 AWG
Conductor - Copper Solid Size A	4 AWG
Range	
Conductor - Copper Solid Size B	4 AWG
Range	

Configuration

Physical Attribute - Number of	4
Crimps Required	
Connector Type	Splice

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	1-1/4 in

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	67 mm
Dimension - B Length inch	1.25 in
Dimension - B Outside Diameter	0.38 in
Dimension - A Outside Diameter	0.42 in
Dimension - Length BB inch	1.25 in
Dimension - Length Overall inch	2.65 in

General

Plated	No
Product Family	Utility Overhead & Underground Distribution>Splices>Reducing Sleeves
Trade Name	HYREDUCER™
Sub Brand	COMPRESSION TERMINAL
Die Index	162
Product Type	Compression
UPC	781810014424
Type	Terminal
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014424

Logistics

Minimum Pack Quantity	1
Pallet Quantity	29000
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)