



YDS021RLY, Tension Sleeve for ACSR, AL, 6201, or 5005

By Burndy

Catalog # [YDS021RLY](#)

Tension Single Sleeve for ACSR, Aluminum, 6201 and 5005



Features

- Single-Sleeve
- Full Tension

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AAAC 5005 Size Range	77.47 (7) kcmil
Conductor - AAAC 6201 Size Range	77.47 (7) kcmil
Conductor - AAAC 6201 Size	77.47 (7) kcmil
Conductor - AL Str Size	2 AWG
Conductor - AAAC 5005 Size	77.47 (7) kcmil
Conductor - AL Str Size Range	2 AWG
Conductor Type	• ACSR C Str-Size • AL C Str-Size
Conductor - ACSR Str Size	• 2 (6/1) Sparrow AWG • 2 (7/1) Sparate AWG
Conductor - ACSR Str Size Range	2 (6/1) Sparrow AWG-2 (7/1) Sparate AWG

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - B Length fraction	7-47/50 in
Dimension - L Length Overall	361 mm
Dimension - B Length inch	7.04 in
Dimension - Outside Diameter	0.8 in
Dimension - Length Overall	14.2 in

General

Plated	N
Trade Name	UNISPLICE™
Die Index	• 167 • 247 • 702 • C
UPC	781810821145
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810821145
UPC 14 Digit GTIN	00781810821145

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2250
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)



A Hubbell brand