

YDS1C3, Copper Single Sleeve Splice

By Burndy
Catalog # [YDS1C3](#)

CU Full Tension Splice, Accommodates Wire: #1 Cu STR (Hard, Medium, or Soft Drawn), Die Index: 459

Features

- Copper Single Sleeve Splice
- Full Tension

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	1 AWG
-----------------------------	-------

Configuration

Physical Attribute - Number of	6
Crimps Required	
Connector Type	Splice

Dimensions

Dimension - L Length Overall	157 mm
mm	



Dimension - B Length inch	2.97 in
Dimension - Outside Diameter inch	0.68 in
Dimension - Length Overall inch	6.18 in
General	
Plated	N
Trade Name	HYSPLICE™
Die Index	• 166 • 459
Oxide Inhibitor Type	Penetrox E
UPC	781810014448
Prefilled Oxide Inhibitor	Y
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014448

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3675
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)