



YDS1RL, Aluminum Full Tension Splice, #1 AWG ACSR

By Burndy
Catalog # [YDS1RL](#)

Al Compression Full Tension Splice, #1 AWG ACSR

Features

- Aluminum Full Tension Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	1 AWG
Conductor - AL Str Size Range	1 AWG
Conductor Type	- ACSR C Str-Size - AL C Str-Size
Conductor - ACSR Str Size	1 (6/1) Robin AWG
Conductor - ACSR Str Size Range	1 (6/1) Robin AWG

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	356 mm
Dimension - Outside Diameter	0.71 in
Dimension - Length Overall	14 in

General

Plated	N
Trade Name	UNISPLICE™
Die Index	245
UPC	621945255876
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	621945255876
UPC 14 Digit GTIN	00621945255876

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2250
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)



A Hubbell brand