

YDS1W, Copper Single Sleeve Splice

By Burndy
Catalog # [YDS1W](#)



CU Full Tension Splice, Accommodates Wire: #1 Cu Sol (Hard, Medium, or Soft Drawn), Die Index: 164

Features

- Copper Single Sleeve Splice
- Full Tension

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	1 AWG
Conductor - Copper Solid Size Range	1 AWG

Configuration

Physical Attribute - Number of Crimps Required	4
Connector Type	Splice

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	2-16/25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	140 mm

Dimension - B Length inch	2.64 in
Dimension - B Outside Diameter inch	0.55 in
Dimension - Outside Diameter inch	0.55 in
Dimension - A Outside Diameter inch	0.55 in
Dimension - Inside Diameter inch	0.32 in
Dimension - Length Overall inch	5.53 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	164
Oxide Inhibitor Type	Penetrox A4
UPC	781810014455
Prefilled Oxide Inhibitor	Y
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014455

Logistics

Minimum Pack Quantity	1
Pallet Quantity	4800
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)