

YDS25, Copper Single Sleeve Splice

By Burndy
Catalog # [YDS25](#)



CU Full Tension Splice, Accommodates Wire: #1 Cu STR (Hard, Medium, or Soft Drawn), Die Index: 164

Features

- Copper Single Sleeve Full Tension Splice
- Full Rated Breaking Strength of Hard, Medium, or Soft Drawn Solid Copper Conductor

Application

For Stranded Copper Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	RUS
Certification - ETL	No
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	1/0 AWG
-----------------------------	---------

Configuration

Physical Attribute - Number of	6
Crimps Required	
Connector Type	Splice

Dimensions

Package Height	0.000 in
----------------	----------

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	137 mm
Dimension - Outside Diameter inch	0.63 in
Dimension - B Length fraction	2-3/5 in
Dimension - B Length inch	2.59 in
Dimension - Length Overall inch	5.38 in

General

Product Family	Utility Overhead & Underground Distribution>Splices>YCS/YDS (Full Tension)
Trade Name	HYSPLICE™
Die Index	165
Oxide Inhibitor Type	Penetrox E
Prefilled Oxide Inhibitor	Y
Plated	No
Sub Brand	HYSPLICE
Product Type	Compression
UPC	781810564820
Type	YDS
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810564820

Logistics

Minimum Pack Quantity	25
Pallet Quantity	4900
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)