



YDS250E, Full Tension Steel Splice

By Burndy
Catalog # [YDS250E](#)

Full-tension steel splice designed for galvanized steel guy, messenger and "static:" conductors. ANSI C119.4 Class 1 (Full Tension),Die index:609

Features

- Full Tension Steel Splice
- Designed for Galvanized Steel Guy, Messenger and "Static" Conductors

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No


Conductor

Conductor - Grade	EHS
Conductor - Galvanized Steel Str Size	1/4 (7) in
Conductor - Galvanized Steel Str Size Range	1/4 (7) in
Conductor - AL Coated Steel Size Range	1/4 (7) in
Conductor - AL Coated Steel Size	1/4 (7) in
Conductor Type	• ACSR C Str-Size • AL C Str-Size

Configuration

Connector Type	Splice
----------------	--------

Dimensions



Package Height	0.000 in
Dimension - B Length fraction	2-49/50 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	171 mm
Dimension - B Length inch	2.98 in
Dimension - Outside Diameter inch	0.59 in
Dimension - Length Overall inch	6.75 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	609
UPC	781810015865
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810015865
UPC 14 Digit GTIN	00781810015865

Logistics

Minimum Pack Quantity	1
Pallet Quantity	5096
Carton Quantity	13

Product Assets

[Catalog \[English\]](#)