



YDS251R, 2-piece, ACSR Splice, includes inner and outer sleeves

By Burndy
Catalog # [YDS251R](#)

Two-piece, full tension ACSR splice consists of steel inner sleeve and aluminum outer sleeve. ANSI C119.4 Class 1 (Full Tension)

Features

- 2-Piece, Full Tension ACSR Splice
- Includes inner and outer sleeves

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	101.8 (12-7)
Conductor Type	• ACSR C Str-Size • AL C Str-Size
Conductor - ACSR Str Size	101.8 (12/7) Petrel kcmil
Conductor - ACSR Str Size Range	101.8 (12/7) Petrel kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - B Length fraction	2-64/79 in
Dimension - Aluminum Sleeve Length inch	22.25 in
Dimension - L Length Overall mm	159 mm

Dimension - B Length inch	2.81 in
Dimension - Outside Diameter inch	1.14 in
Dimension - Steel Sleeve Length inch	6.25 in
Dimension - Length Overall inch	6.25 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	• 253 • 316
Die Index - Element A	253
Die Index - Element B	316
UPC	781810092309
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810092309
UPC 14 Digit GTIN	00781810092309

Logistics

Minimum Pack Quantity	15
Pallet Quantity	900
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)



A Hubbell brand