



YDS25F, Copper Full Tension Splice

By Burndy
Catalog # [YDS25F](#)



CU Full Tension Splice, Accommodates Wire: 1/0F
COPPERWELD, Die Index: 568

Features

- Copper Full Tension Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - CopperWeld Str Size Range	1/0 F AWG
Conductor - CopperWeld Str Size	1/0 F AWG
Conductor - Copper Str Size	1/0 F AWG

Configuration

Physical Attribute - Number of Crimps Required	6
Connector Type	Splice

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	211 mm
Dimension - B Length inch	3.99 in
Dimension - Outside Diameter inch	0.76 in
Dimension - Length Overall inch	8.30 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	568
UPC	781810000427
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810000427

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2250
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)