



YDS25R, 2-piece, ACSR Splice, includes inner and outer sleeves

By Burndy  
Catalog # [YDS25R](#)

2-piece, full tension ACSR splice consists of steel inner sleeve and AL outer sleeve, ANSI C119.4 Class 1 (Full Tension), Conductor:1/0 (6/1) Raven

Features

- 2-Piece ACSR Splice
- Includes inner and outer sleeves

Specifications

|                               |    |
|-------------------------------|----|
| Certification - ETL           | No |
| Certification - UL Recognized | No |
| Standards - RoHS Compliance   | CM |
| Status                        |    |
| Certification - cULus         | No |
| UL Listed                     | No |
| Certification - CSA Approved  | No |

Conductor

|                                 |                     |
|---------------------------------|---------------------|
| Conductor Type                  | ACSR C Str-Size     |
| Conductor - ACSR Str Size       | 1/0 (6/1) Raven AWG |
| Conductor - ACSR Str Size Range | 1/0 (6/1) Raven AWG |

Configuration

|                |        |
|----------------|--------|
| Connector Type | Splice |
|----------------|--------|

Dimensions

|                                         |           |
|-----------------------------------------|-----------|
| Package Height                          | 0.000 in  |
| Dimension - Aluminum Sleeve Length inch | 17 in     |
| Package Weight                          | 0.000 lb. |
| Package Length                          | 0.000 in  |

|                                      |          |
|--------------------------------------|----------|
| Package Width                        | 0.000 in |
| Dimension - L Length Overall mm      | 121 mm   |
| Dimension - Steel Sleeve Length inch | 4.75 in  |
| Dimension - Length Overall inch      | 4.75 in  |

General

|                           |                                                                     |
|---------------------------|---------------------------------------------------------------------|
| Plated                    | N                                                                   |
| Trade Name                | HYSPLICE™                                                           |
| Die Index                 | <ul style="list-style-type: none"><li>• 242</li><li>• 243</li></ul> |
| Die Index - Element A     | 242                                                                 |
| Die Index - Element B     | 243                                                                 |
| UPC                       | 781810015506                                                        |
| Prefilled Oxide Inhibitor | Y                                                                   |
| Material                  | Aluminum                                                            |
| Plating Type              | Unplated                                                            |
| UPC 12 Digit              | 781810015506                                                        |
| UPC 14 Digit GTIN         | 00781810015506                                                      |

Logistics

|                       |      |
|-----------------------|------|
| Minimum Pack Quantity | 1    |
| Pallet Quantity       | 2400 |
| Carton Quantity       | 25   |

Product Assets

[Catalog \[English\]](#)