



# YDS26, Copper Full Tension Sleeve

By Burndy  
Catalog # [YDS26](#)



Hysplice, 2/0 (7, 12, 19) str., 6 in L, Full Tension Sleeve for Stranded Copper Conductors

## Features

- Copper Full Tension Sleeve for Copper Conductors
- Full Rated Breaking Strength of Hard, Medium, or Soft Drawn Solid Copper Conductor

## Application

For Stranded Copper Conductors

## Specifications

|                               |                                                     |
|-------------------------------|-----------------------------------------------------|
| Certification - UL Recognized | No                                                  |
| Buy American Compliant        | Contact Manufacturer                                |
| Certification - cULus         | No                                                  |
| Buy America(n) Qualified      | TAA Compliant (All status valid till December 2026) |
| Certification - ETL           | No                                                  |
| Standards - RoHS Compliance   | CM                                                  |
| Status                        |                                                     |
| UL Listed                     | No                                                  |
| Certification - CSA Approved  | No                                                  |

## Conductor

|                             |         |
|-----------------------------|---------|
| Conductor - Copper Str Size | 2/0 AWG |
|-----------------------------|---------|

## Configuration

|                |        |
|----------------|--------|
| Connector Type | Splice |
|----------------|--------|

## Dimensions

|                                 |           |
|---------------------------------|-----------|
| Package Height                  | 0.000 in  |
| Package Weight                  | 0.000 lb. |
| Package Length                  | 0.000 in  |
| Package Width                   | 0.000 in  |
| Dimension - L Length Overall mm | 151 mm    |

|                                     |            |
|-------------------------------------|------------|
| Dimension - Outside Diameter inch   | 0.71 in    |
| Dimension - A Outside Diameter inch | 0.71 in    |
| Dimension - B Length fraction       | 2-17/20 in |
| Dimension - B Length inch           | 2.85 in    |
| Dimension - B Outside Diameter inch | 0.71 in    |
| Dimension - Length Overall inch     | 5.95 in    |

## General

|                           |                                                                            |
|---------------------------|----------------------------------------------------------------------------|
| Product Family            | Utility Overhead & Underground Distribution>Splices>YCS/YDS (Full Tension) |
| Trade Name                | HYSPLICE™                                                                  |
| Die Index                 | 166                                                                        |
| Oxide Inhibitor Type      | Penetrox E                                                                 |
| Prefilled Oxide Inhibitor | Y                                                                          |
| Plated                    | No                                                                         |
| Sub Brand                 | HYSPLICE                                                                   |
| Product Type              | Compression                                                                |
| UPC                       | 781810564844                                                               |
| Type                      | YDS                                                                        |
| Material                  | Copper                                                                     |
| Plating Type              | Unplated                                                                   |
| UPC 14 Digit GTIN         | 00781810564844                                                             |

## Logistics

|                       |      |
|-----------------------|------|
| Minimum Pack Quantity | 1    |
| Pallet Quantity       | 4350 |
| Carton Quantity       | 25   |

## Product Assets

[Catalog \[English\]](#)