



YDS261R, 2-piece, ACSR Splice, includes inner and outer sleeves

By Burndy
Catalog # [YDS261R](#)

Two-piece, full tension ACSR splice consists of steel inner sleeve and aluminum outer sleeve. ANSI C119.4 Class 1 (Full Tension)

Features

- 2-Piece, Full Tension ACSR Splice
- Includes inner and outer sleeves

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	134.6 (12-7)
Conductor Type	• ACSR C Str-Size • AL C Str-Size
Conductor - ACSR Str Size	134.6 (12/7) Leghorn kcmil
Conductor - ACSR Str Size Range	134.6 (12/7) Leghorn kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - Aluminum Sleeve Length inch	22.25 in
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	219 mm
Dimension - Steel Sleeve Length inch	8.625 in
Dimension - Length Overall inch	8.63 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	• 305 • 316
Die Index - Element A	305
Die Index - Element B	316
UPC	781810099698
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810099698
UPC 14 Digit GTIN	00781810099698

Logistics

Minimum Pack Quantity	1
Pallet Quantity	900
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)



A Hubbell brand