



YDS26F, Single Sleeve Full Tension Splice

By Burndy
Catalog # YDS26F



CU Full Tension Splice, Accommodates Wire: 2/0F
COPPERWELD, Die Index: 552

Features

- Single Sleeve, Full Tension Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - CopperWeld Str	2/0 F AWG
Size Range	
Conductor - CopperWeld Str	2/0 F
Size	
Conductor - Copper Str Size	2/0 F AWG

Configuration

Physical Attribute - Number of	6
Crimps Required	
Connector Type	Splice

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	4-3/8 in

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	234 mm
mm	
Dimension - B Length inch	4.37 in
Dimension - Outside Diameter	0.86 in
inch	
Dimension - Length Overall	9.22 in
inch	

General

Plated	N
Trade Name	HYSPLICE™
Die Index	552
UPC	781810014622
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014622

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1575
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)