



YDS26R, 2-piece, ACSR Splice, includes inner and outer sleeves

By Burndy
Catalog # [YDS26R](#)

2-piece, full tension ACSR splice consists of steel inner sleeve and AL outer sleeve, ANSI C119.4 Class 1 (Full Tension), Conductor: 2/O (6/1) Quail

Features

- 2-Piece, Full Tension ACSR Splice
- Includes inner and outer sleeves

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Cmpt Size Range	2/O AWG
Conductor - ACSR Cmpt Size	2/O AWG
Conductor Type	• ACSR C Str-Size • AL C Str-Size
Conductor - ACSR Str Size	2/O (6/1) Quail AWG
Conductor - ACSR Str Size Range	2/O (6/1) Quail AWG

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - Aluminum Sleeve Length inch	19.75 in
Package Weight	0.000 lb.
Package Length	0.000 in

Package Width	0.000 in
Dimension - L Length Overall mm	502 mm
Dimension - B Length inch	19.75 inch
Dimension - Outside Diameter inch	0.7 in
Dimension - Steel Sleeve Length inch	5.25 in
Dimension - Length Overall inch	19.73 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	• 242 • 245
Die Index - Element A	242
Die Index - Element B	245
UPC	781810015513
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810015513
UPC 14 Digit GTIN	00781810015513

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1920
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)