



YDS26RLY, Aluminum Single Sleeve Full Tension Splice

By Burndy
Catalog # [YDS26RLY](#)

AL Compression Splices - Single Sleeve Full Tension,
Accommodates: AAC, ACSR and AAAC, Length: 15 IN L

Features

- Aluminum Compression Single Sleeve Splice
- Full Tension

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Cmpt Size Range	2/0 AWG
Conductor - ACSR Cmpt Size	2/0 AWG
Conductor - AAAC 5005 Size Range	155.4 (7) kcmil
Conductor - AAAC 6201 Size Range	155.4 (7) kcmil
Conductor - AAAC 6201 Size	155.4 (7) kcmil
Conductor - AL Str Size	2/0 AWG
Conductor - AAAC 5005 Size	155.4 (7) kcmil
Conductor - AL Str Size Range	2/0 AWG
Conductor Type	• ACSR C Str-Size • AL C Str-Size
Conductor - ACSR Str Size	2/0 (6/1) Quail AWG
Conductor - ACSR Str Size Range	2/0 (6/1) Quail AWG

Configuration

Connector Type	Splice
----------------	--------



Dimensions

Package Height	0.000 in
Dimension - B Length fraction	7-11/25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	381 mm
Dimension - B Length inch	7.44 in
Dimension - Outside Diameter inch	0.83 in
Dimension - Length Overall inch	15 in

General

Plated	N
Trade Name	UNISPLICE™
Die Index	659
UPC	781810821084
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810821084
UPC 14 Digit GTIN	00781810821084

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2400
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)