



YDS27, Copper Single Sleeve Full Tension Splice



By Burndy
Catalog # [YDS27](#)

CU Full Tension Splice, Accommodates Wire: 3/0 Cu STR (Hard, Medium, or Soft Drawn), Die Index: 167

Features

- Copper Single Sleeve Full Tension Splice
- Full Rated Breaking Strength of Hard, Medium, or Soft Drawn Solid Copper Conductor

Application

For Stranded Copper Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	3/0 AWG
-----------------------------	---------

Configuration

Physical Attribute - Number of	7
Crimps Required	
Connector Type	Splice

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	173 mm
Dimension - Outside Diameter inch	0.79 in
Dimension - B Length fraction	3-2/7 in
Dimension - B Length inch	3.29 in
Dimension - Length Overall inch	6.83 in

General

Product Family	Utility Overhead & Underground Distribution>Splices>YCS/YDS (Full Tension)
Trade Name	HYSPLICE™
Die Index	167
Oxide Inhibitor Type	Penetrox E
Prefilled Oxide Inhibitor	Y
Plated	No
Sub Brand	HYSPLICE
Product Type	Compression
UPC	781810014639
Type	YDS
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014639

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2450
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)