



YDS271R, 2-piece, ACSR Splice, includes inner and outer sleeves

By Burndy
Catalog # [YDS271R](#)

Two-piece, full tension ACSR splice consists of steel inner sleeve and aluminum outer sleeve. ANSI C119.4 Class 1 (Full Tension)

Features

- 2-Piece ACSR Splice
- Includes inner and outer sleeves

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Type	• ACSR C Str-Size • AL C Str-Size
Conductor - ACSR Str Size	159 (12/7) Guinea kcmil
Conductor - ACSR Str Size Range	159 (12/7) Guinea kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - Aluminum Sleeve Length inch	25.625 in
---	-----------

Dimension - L Length Overall mm	203 mm
Dimension - Steel Sleeve Length inch	8 in
Dimension - Length Overall inch	8 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	• 255 • 317
Die Index - Element A	255
Die Index - Element B	317
UPC	781810090923
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810090923
UPC 14 Digit GTIN	00781810090923

Logistics

Minimum Pack Quantity	1
Pallet Quantity	600
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)



A Hubbell brand