



YDS27AT, Aluminum Full Tension Sleeve

By Burndy
Catalog # [YDS27AT](#)

Aluminum HYSPLICE, 7-1/4 in L, Full Tension Sleeve for Aluminum Conductors, Die index: 247



Features

- Full-Tension sleeve made of aluminum tubing with staked-in cable stop
- Sizes 1/0 and larger feature a taper for gradual transition of stress
- Pre-Filled with PENETROX Joint Compound and Capped

Application

For All Aluminum Compressed And Compact Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	3/0 (7) AWG
Conductor - ACAR Str Size	3/0 (7) AWG
Conductor - AL Str Size	3/0 AWG
Conductor - AL Str Size Range	3/0 AWG

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	184 mm
Dimension - Outside Diameter inch	0.77 in
Dimension - B Length fraction	3-14/25 in
Dimension - B Length inch	3.56 in
Dimension - Length Overall inch	7.25 in

General

Trade Name	HYSPLICE™
Die Index	247
Prefilled Oxide Inhibitor	Y
Insulation	Y
Plated	N
Sub Brand	HYSPLICE
UPC	781810015544
Type	YDS-AT
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810015544
UPC 14 Digit GTIN	00781810015544

Logistics

Minimum Pack Quantity	1
Pallet Quantity	9800
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)