



YDS27R, 2-piece, ACSR Splice, includes inner and outer sleeves

By Burndy
Catalog # [YDS27R](#)

2-piece, full tension ACSR splice consists of steel inner sleeve and AL outer sleeve, ANSI C119.4 Class 1 (Full Tension), Conductor: 3/0 (6/1) Pigeon

Features

- 2-Piece, Full Tension HYSPLICE consists of aluminum outer sleeve and steel inner sleeve
- Tapered out sleeve provides gradual transition of stress
- Filler hole provided for PENETROX Joint Compound
- Sizes 1/0 and larger come supplied with plugs for filler hole

Application

For ACSR, Compressed And Compact Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Cmpt Size Range	3/0 AWG
Conductor - ACSR Cmpt Size	3/0 AWG
Conductor - ACSR Str Size	3/0 (6/1) Pigeon AWG
Conductor - ACSR Str Size Range	3/0 (6/1) Pigeon AWG
Conductor Type	• ACSR C Str-Size • AL C Str-Size

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
----------------	----------

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	133 mm
Dimension - Outside Diameter inch	0.78 in
Dimension - Steel Sleeve Length inch	5.25 in
Dimension - B Length fraction	2-1/2 in
Dimension - Aluminum Sleeve Length inch	16.75 in
Dimension - B Length inch	2.5 in
Dimension - Length Overall inch	5.25 in

General

Trade Name	HYSPLICE™
Die Index	• 248 • 247
Die Index - Element A	247
Die Index - Element B	248
Prefilled Oxide Inhibitor	Y
Plated	N
Sub Brand	HYSPLICE
UPC	781810015551
Type	YDS-R SET
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810015551
UPC 14 Digit GTIN	00781810015551

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1920
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)