



YDS27RLY, Aluminum Single Sleeve Full Tension Splice

By Burndy
Catalog # [YDS27RLY](#)

AL Compression Splices - Single Sleeve Full Tension,
Accommodates: AAC, ACSR and AAAC, Length: 21 IN L



Features

- Aluminum Single Sleeve Full Tension Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AAAC 5005 Size Range	195.7 (7) kcmil
Conductor - AAAC 6201 Size Range	195.7 (7) kcmil
Conductor - AAAC 6201 Size	195.7 (7) kcmil
Conductor - AL Str Size	3/0 AWG
Conductor - AAAC 5005 Size	195.7 (7) kcmil
Conductor - AL Str Size Range	3/0 AWG
Conductor Type	- ACSR C Str-Size - AL C Str-Size
Conductor - ACSR Str Size	3/0 (6/1) Pigeon AWG
Conductor - ACSR Str Size Range	3/0 (6/1) Pigeon AWG

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	10-11/25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	533 mm
Dimension - B Length inch	10.44 in
Dimension - Outside Diameter	0.91 in
Dimension - Length Overall	21 in

General

Plated	N
Trade Name	UNISPLICE™
Die Index	658
UPC	781810015568
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810015568
UPC 14 Digit GTIN	00781810015568

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1800
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)