



YDS28F, Single Sleeve Full Tension Splice

By Burndy
Catalog # [YDS28F](#)

CU Full Tension Splice, Accommodates Wire: 4/0F
COPPERWELD, Die Index: 331

Features

- Single Sleeve, Copper Full Tension Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - CopperWeld Str Size Range	4/0 F AWG
Conductor - CopperWeld Str Size	4/0 F AWG
Conductor - Copper Str Size	4/0 F AWG

Configuration

Physical Attribute - Number of Crimps Required	4
Connector Type	Splice

Dimensions

Dimension - B Length fraction	5-3/7 in
Dimension - L Length Overall mm	289 mm
Dimension - B Length inch	5.43 in
Dimension - Outside Diameter inch	0.96 in
Dimension - Length Overall inch	11.38 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	331
UPC	781810014127
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014127

Logistics

Minimum Pack Quantity	1
Pallet Quantity	945
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)