



YDS28R, 2-piece, ACSR Splice, includes inner and outer sleeves

By Burndy
Catalog # [YDS28R](#)

Hysplice; 4/0 (6-1) AWG; 5-1/8 Steel 18-7/8 Alum.

Features

- 2-Piece ACSR Splice
- Includes inner and outer sleeves

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Cmpt Size Range	4/0 AWG
Conductor - ACSR Cmpt Size	4/0 AWG
Conductor Type	• ACSR C Str-Size • AL C Str-Size
Conductor - ACSR Str Size	4/0 (6/1) Penguin AWG
Conductor - ACSR Str Size Range	4/0 (6/1) Penguin AWG

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - Aluminum Sleeve Length inch	18.875 in

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	130 mm
Dimension - Steel Sleeve Length inch	5.125 in
Dimension - Length Overall inch	5.12 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	• 248 • 249
Die Index - Element A	248
Die Index - Element B	249
UPC	781810015582
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810015582
UPC 14 Digit GTIN	00781810015582

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1920
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)



A Hubbell brand