



YDS28RE, HYSPLICE Assembly, 4/0 ACSR / AL

By Burndy
Catalog # [YDS28RE](#)

HYSPLICE ASSEMBLY

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Cmpt Size Range	4/0 AWG
Conductor - ACSR Cmpt Size	4/0 AWG
Conductor - AL Str Size	4/0 AWG
Conductor - AL Str Size Range	4/0 AWG
Conductor Type	• ACSR C Str-Size • AL C Str-Size
Conductor - ACSR Str Size	4/0 (6/1) Penguin AWG
Conductor - ACSR Str Size Range	4/0 (6/1) Penguin AWG

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	2-8/17 in

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	478 mm
Dimension - B Length inch	2.47 in
Dimension - Outside Diameter	0.88 in
Dimension - Length Overall	18.81 in

General

Plated	N
Die Index - Element B	249
UPC	781810081235
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810081235
UPC 14 Digit GTIN	00781810081235

Logistics

Minimum Pack Quantity	25
Pallet Quantity	2400
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)