



# YDS2C3, Copper Single Sleeve Full Tension Splice

By Burndy  
Catalog # [YDS2C3](#)

CU Full Tension Splice, Accommodates Wire: #2 (3) Cu STR (Hard, Medium, or Soft Drawn), Die Index: 163

## Features

- Copper Single Sleeve Full Tension Splice
- Full Rated Breaking Strength of Hard, Medium, or Soft Drawn Solid Copper Conductor

## Application

For Stranded Copper Conductors

## Specifications

|                                    |                      |
|------------------------------------|----------------------|
| Certification - UL Recognized      | No                   |
| Buy American Compliant             | Contact Manufacturer |
| Certification - cULus              | No                   |
| Buy America(n) Qualified           | Contact Manufacturer |
| Industry Standard(s)               | RUS                  |
| Certification - ETL                | No                   |
| Standards - Industry Standards Met | RUS                  |
| Standards - RoHS Compliance        | CM                   |
| Status                             |                      |
| UL Listed                          | No                   |
| Certification - CSA Approved       | No                   |

## Conductor

|                             |       |
|-----------------------------|-------|
| Conductor - Copper Str Size | 2 AWG |
|-----------------------------|-------|

## Configuration

|                                |        |
|--------------------------------|--------|
| Physical Attribute - Number of | 2      |
| Crimps Required                |        |
| Connector Type                 | Splice |

## Dimensions

|                |          |
|----------------|----------|
| Package Height | 0.000 in |
|----------------|----------|



|                                   |            |
|-----------------------------------|------------|
| Package Weight                    | 0.000 lb.  |
| Package Length                    | 0.000 in   |
| Package Width                     | 0.000 in   |
| Dimension - L Length Overall mm   | 94 mm      |
| Dimension - Outside Diameter inch | 0.53 in    |
| Dimension - B Length fraction     | 1-18/25 in |
| Dimension - B Length inch         | 1.72 in    |
| Dimension - Length Overall inch   | 3.69 in    |

## General

|                           |                                                                            |
|---------------------------|----------------------------------------------------------------------------|
| Product Family            | Utility Overhead & Underground Distribution>Splices>YCS/YDS (Full Tension) |
| Trade Name                | HYSPLICE™                                                                  |
| Die Index                 | 163                                                                        |
| Oxide Inhibitor Type      | Penetrox E                                                                 |
| Prefilled Oxide Inhibitor | Y                                                                          |
| Plated                    | No                                                                         |
| Sub Brand                 | HYSPLICE                                                                   |
| Product Type              | Compression                                                                |
| UPC                       | 781810820919                                                               |
| Type                      | YDS - C                                                                    |
| Material                  | Copper                                                                     |
| Plating Type              | Unplated                                                                   |
| UPC 14 Digit GTIN         | 00781810820919                                                             |

## Logistics

|                       |       |
|-----------------------|-------|
| Minimum Pack Quantity | 100   |
| Pallet Quantity       | 11100 |
| Carton Quantity       | 100   |

## Product Assets

[Catalog \[English\]](#)