

YDS2CA, Aluminum Full Tension Splice, Staked Cable Stop

By Burndy
Catalog # [YDS2CA](#)

Full tension aluminum splice with staked in cable stop. ANSI C199.4 Class 1 (Full Tension), Conductor:2(7)



Features

- Full-Tension sleeve made of aluminum tubing with staked-in cable stop
- Sizes 1/0 and larger feature a taper for gradual transition of stress
- Pre-Filled with PENETROX Joint Compound and Capped

Application

For All Aluminum Compressed And Compact Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	2 (7) AWG
Conductor - ACAR Str Size	2 (7) AWG
Conductor - ACSR Cmpt Size Range	2 AWG
Conductor - ACSR Cmpt Size	2 AWG
Conductor - AL Str Size	2 AWG
Conductor - AL Str Size Range	2 AWG
Conductor Type	• ACSR C Str-Size • AL C Str-Size

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	99 mm
Dimension - Outside Diameter inch	0.5 in
Dimension - B Length fraction	1-22/25 in
Dimension - B Length inch	1.88 in
Dimension - Inside Diameter inch	1 in
Dimension - Length Overall inch	3.88 in

General

Trade Name	HYSPLICE™
Die Index	163
Prefilled Oxide Inhibitor	Y
Plated	N
Sub Brand	HYSPLICE
UPC	781810015339
Type	YDS-A
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810015339
UPC 14 Digit GTIN	00781810015339

Logistics

Minimum Pack Quantity	100
Pallet Quantity	9000
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)