



YDS2F, Copper Single Sleeve Full Tension Splice

By Burndy
Catalog # [YDS2F](#)



CU Full Tension Splice, Accommodates Wire: 2F COPPERWELD,
Die Index: 329

Features

- Copper Single Sleeve Full Tension Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - CopperWeld Str Size	2F
---------------------------------	----

Configuration

Physical Attribute - Number of Crimps Required	4
Connector Type	Splice

Dimensions

Dimension - B Length fraction	2-3/4 in
-------------------------------	----------

Dimension - L Length Overall mm	150 mm
Dimension - B Length inch	2.75 in
Dimension - Outside Diameter inch	0.61 in
Dimension - Length Overall inch	5.92 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	329
UPC	781810014462
Prefilled Oxide Inhibitor	Y
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014462

Logistics

Minimum Pack Quantity	1
Pallet Quantity	4350
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)