



YDS2KT, Copper Single Sleeve Full Tension Splice

By Burndy
Catalog # [YDS2KT](#)

CU Full Tension Splice, Accommodates Wire: 2A COPPERWELD,
Die Index: 205



Features

- Copper Single Sleeve Full Tension Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - CopperWeld Str Size	2A
---------------------------------	----

Configuration

Physical Attribute - Number of Crimps Required	8
Connector Type	Splice

Dimensions

Dimension - B Length fraction	3-18/25 in
-------------------------------	------------

Dimension - L Length Overall mm	195 mm
Dimension - B Length inch	3.72 in
Dimension - Length Overall inch	7.68 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	205
UPC	781810014479
Prefilled Oxide Inhibitor	Y
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014479

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3675
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)