



YDS2RE, HYSPLICE Assembly, 2 ACSR / AL

By Burndy
Catalog # [YDS2RE](#)

HYSPLICE - ASSEMBLY

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	UI
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Cmpt Size Range	2 AWG
Conductor - ACSR Cmpt Size	2 AWG
Conductor - AL Str Size	2 AWG
Conductor - AL Str Size Range	2 AWG
Conductor Type	• ACSR C Str-Size • AL C Str-Size
Conductor - ACSR Str Size	2 (6/1) Sparrow AWG
Conductor - ACSR Str Size Range	2 (6/1) Sparrow AWG

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - B Length fraction	1-49/50 in
Dimension - L Length Overall	433 mm
Dimension - B Length inch	1.98 in
Dimension - Outside Diameter	0.52 in
Dimension - Length Overall	17.05 in

General

Plated	N
Die Index - Element B	693
UPC	781810179277
Prefilled Oxide Inhibitor	Y
Material	Mixed
Plating Type	Unplated
UPC 12 Digit	781810179277
UPC 14 Digit GTIN	00781810179277

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)