



YDS2RLS20, Aluminum Single Sleeve Full Tension Splice

By Burndy
Catalog # [YDS2RLS20](#)

Al Compression Full Tension Splice, #2 Smooth Body ACSR #200 Grade

Features

- Aluminum Single Sleeve Full Tension Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	2 AWG
Conductor - AL Str Size Range	2 AWG
Conductor Type	- ACSR C Str-Size - AL C Str-Size
Conductor - ACSR Str Size	2 (6/1) Sparrow AWG
Conductor - ACSR Str Size Range	2 (6/1) Sparrow AWG

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
----------------	----------

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	357 mm
Dimension - Length Overall inch	14.05 in

General

Plated	N
Trade Name	UNISPLICE™
Die Index	249
UPC	621945068124
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	621945068124
UPC 14 Digit GTIN	00621945068124

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2250
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)