



YDS301AT, Aluminum Full Tension Sleeve

By Burndy
Catalog # [YDS301AT](#)



HYSPLICE™, 336.4 (19, 37), 9-7/8 in L, Full Tension Sleeve for All Aluminum Compressed and Compact Conductors

Features

- Full-Tension sleeve made of aluminum tubing with staked-in cable stop
- Sizes 1/0 and larger feature a taper for gradual transition of stress
- Pre-Filled with PENETROX Joint Compound and Capped

Application

For All Aluminum Compressed And Compact Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Cmpt Size Range	336.4
Conductor - ACSR Cmpt Size	336.4
Conductor - AL Str Size	336.4
Conductor - AL Str Size Range	336.4
Conductor - ACSR Str Size	• 336.4 (18/1) Merlin • 336.4 (26/7) Linnet • 336.4 (30/7) Oriole
Conductor - ACSR Str Size Range	336.4 (18/1) Merlin-336.4 (30/7) Oriole
Conductor Type	• ACSR C Str-Size • AL C Str-Size

Configuration

Connector Type Splice

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	251 mm
Dimension - Outside Diameter inch	1.06 in
Dimension - B Length fraction	4-22/25 in
Dimension - B Length inch	4.88 in
Dimension - Length Overall inch	9.88 in

General

Trade Name	HYSPLICE™
Die Index	321
Prefilled Oxide Inhibitor	Y
Insulation	Y
Plated	N
Sub Brand	HYSPLICE
UPC	781810015902
Type	YDS-AT
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810015902
UPC 14 Digit GTIN	00781810015902

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2700
Carton Quantity	30

Product Assets

[Catalog \[English\]](#)